

X-ray Photon Counting: Sensor Calibration, Pulse Pileup Correction, Dynamic Range & Spectral Detection

A new statistical model enhances X-ray photon counting detectors by eliminating readout noise, compensating for pulse pileup, increasing dynamic range, and providing enhanced spectral imaging for applications like airport security.

Charge coupled device (CCD) sensors are the current state of the art in X-ray detection; however, by simply detecting and integrating the amount of X-ray charge deposited on each sensor of the pixel in the sensor over a period of time, CCDs are subject to readout noise. CCDs also suffer from detector pulse pileup, where a photon strikes the detector before the previous photon has been discharged, causing an underestimation of the number of photons actually striking the sensors. As a result of their limited sensing abilities, CCDs have a limited linear dynamic range and their spectral imaging is not strong.

Researchers at Purdue University have developed a statistical model for X-ray photon counting, representing the newest challenger to the state of the art in X-ray detection. The statistical model was developed to model the observed energy distribution across an array of photon counting sensors. Specifically, the model was used to mathematically calibrate the response of each pixel in the detector for its gain, variance, and charge sharing. While most of the potential advantages remain untapped, it is known that X-ray photon counting can eliminate readout noise. Also, the X-ray photon sensors can detect the distribution of observed photon energies, which inherently contain more information than the simple measurement of the number of photons that struck the detector. This model can also compensate mathematically for detector pulse pileup, providing a more accurate estimate of the X-ray photon distribution. Applications of the statistical model can be used to calibrate X-ray photon counting detectors more accurately, compensate for pulse pileup effects, increase the linear dynamic range of the detectors, and provide enhanced spectral imaging capabilities far beyond the previously demonstrated two-color separation.

Technology ID

2014-SIMP-66854

Category

Robotics &

Automation/Perception &

Sensing

Artificial Intelligence & Machine

Learning/AI-Integrated Imaging

Systems & Industrial Vision and

Inspection

Authors

Ryan Muir

Nicholas Pogradichniy

Garth Jason Simpson

Further information

Aaron Taggart

adtaggart@prf.org

View online



Advantages:

- Eliminates readout noise
- Scans contain more information

Potential Applications:

- X-ray photon counting calibration
- Airport security

TRL: 3

Intellectual Property:

Provisional-Patent, 2014-05-12, United States | Utility Patent, 2015-05-11, United States | CON-Patent, 2018-12-04, United States

Keywords: X-ray photon counting, statistical model, X-ray detection, detector pulse pileup, spectral imaging, linear dynamic range, readout noise, photon counting sensors, CCD sensors, X-ray photon distribution, Chemistry and Chemical Analysis, Detection, Photons, Sensors